

DISTRIBUTOR/AGENT:	DATE OF ORDER:
	DATE OF DELIVERY:
	NAME OF THE ADDRESSEE/USER:



ACCORDING to THE ISO  
7176/19 and  
ANSI RESNA WC/19

size **Small**

size **Medium**

Frame colour: **black**

Upholstery colour:  **dark grey/green-green**

**dark grey/pink-pink**

**light grey/green-green**

**light grey/pink-pink**

**M  
E  
A  
S  
U  
R  
E  
S**



	A (cm)	B (cm)	C (cm)	D (cm)	E (cm)	F (cm)	G (degrees)	J (degrees)	H (cm)	I (cm)	L (cm)	M (cm)	N (cm)	O (cm)	P (cm)	Q (cm)	R (cm)	S (cm)	max. load	frame weight	seat weight	total weight
<b>Small</b>	20-30	52-62	37	52	20-30	14-30	0°-35°	35°	100-110	57	67-96	35	88	33	82	50	81	90-120	35 kg	9,5 kg	8,5 kg	18 kg
<b>Medium</b>	25-36	60-75	46	55	30-40	20-38	5°-30°	40°	112-127	62	80-107	37	112	39	94	52	94	115-140	45 kg	11 kg	12,7 kg	23,7 kg

Hypen-separated numbers indicate the minimum and maximum range of adjustment

**SEAT UNIT, the only one with a tilt-in-space system incorporated in the seat**

- HEADREST incorporated in the backrest: your child's head is always supported during the tilt adjustments of the seat and of the backrest, also without accessories.
- Rigid BACKREST, reclinable and adjustable in height. The hinge coincides with the child's pelvis physiological fulcrum.
- Tilt-in-space SEAT, adjustable in width and depth. Reversible (size Small, base 869).
- Fireproof, recyclable FABRIC. Colours durable and highly resistant to sweat, light, dry cleaning and washing. Maximum resistance to rubbing. Oeko-Tex Certificate - for textile products intended for all fabrics that are in direct contact with the skin, a guarantee of quality and safety for health.
- Tip-up FOOTREST, flexion-extension adjustable, with legrest adjustable in height and tilt; the hinge coincides with the child's knee physiological fulcrum.

**869 OUTDOOR four wheels base - CRASH TESTED ISO 7176/19 and ANSI RESNA WC/19**

- Foldable aluminium FRAME. Push-handle adjustable in tilt: it adapts to the mother's height and reduces the encumbrance of the pushchair.
- Puncture proof WHEELS, light and easy to push on every surface: front 17 cm with directional locks; rear 25 cm (size Small) or 30 cm (size Medium), with shock absorbers and independent drum brakes.

**856 - 851 indoor high-low bases, 850 indoor compact floor base**

- Foldable FRAME in steel. Adjustable in height. It is easy and safe to use, thanks to a gas spring mechanism, hand lever (base 851) and foot pedal (base 856)
- 10 cm swivelling WHEELS with brakes (for base 856)
- 7.5 cm swivelling WHEELS with brakes (for base 851)



**Attention!**  
Read carefully the user and  
maintenance manual

ADDITIONAL COMPONENTS	<input type="checkbox"/> <b>863</b> Multiadjustable Headrest with parietal supports 	<input type="checkbox"/> <b>852</b> Headrest with parietal supports 	<input type="checkbox"/> <b>942</b> Ergonomic headrest for Bug Small <input type="checkbox"/> S <input type="checkbox"/> M 	<input type="checkbox"/> <b>835</b> Shaped headrest 	<input type="checkbox"/> <b>838</b> Adjustable lateral supports 	<input type="checkbox"/> <b>894</b> 45° pelvic belt 
	<input type="checkbox"/> <b>868</b> Adjustable wrappable and flexible trunk supports 	<input type="checkbox"/> <b>834</b> Padded abduction block 	<input type="checkbox"/> <b>834R</b> Adjustable padded abduction block 	<input type="checkbox"/> <b>853</b> Vest harness 	<input type="checkbox"/> <b>903</b> Five point vest harness 	<input type="checkbox"/> <b>906</b> Five point harness 
	<input type="checkbox"/> <b>920</b> 4 point belt 	<input type="checkbox"/> <b>827</b> Foot straps 	<input type="checkbox"/> <b>839</b> Adjustable front handle 	<input type="checkbox"/> <b>824</b> Adjustable transparent tray 	<input type="checkbox"/> <b>824B</b> Wide tray only for 850-851-856 indoor bases. 	
	<input type="checkbox"/> <b>935</b> Oxygen bottle holder Maximum dimensions of the oxygen bottle: height 600 mm (valve included) - diameter 140 mm. 	<input type="checkbox"/> <b>911</b> Vent tray 	<input type="checkbox"/> <b>819</b> Canopy black/green <input type="checkbox"/> <b>819</b> Canopy black/pink 	<input type="checkbox"/> <b>825</b> Rain cover (to fix at the canopy 819) for 869 base 	<input type="checkbox"/> <b>818</b> Thermal cover 	
	<input type="checkbox"/> <b>892</b> Padded covering for footrest 	<input type="checkbox"/> <b>858</b> Net basket for 869 base 	<input type="checkbox"/> <b>922</b> Bottle holder for 869 base 	<input type="checkbox"/> <b>891</b> Set of 4 tie down hooks for the forward-facing transport of the pushchair in a motor vehicle (private/cars, buses...). Only for 869 base 		
	<input type="checkbox"/> <b>817</b> Leg straps 	<input type="checkbox"/> <b>850</b> Indoor compact floor base 	<input type="checkbox"/> <b>856</b> Indoor high-low feeding base 			

